



DEEP SCREW MOUNT STEEL STUD BOX WITH QUICK/CLICK

S122RS | [Pass & Seymour](#)

FEATURES & BENEFITS

Deep Single-Gang Switch and Outlet Box with Quick/Click® and captive combo-head self-tapping mounting screws on each end. Two Quick/Entries® on each end. Extra deep for dimmers, GFCIs, and thermostats, yet suitable for 2 x 4 construction. Easy to install and constructed of durable, impact-resistant thermoplastic. 100 pack.



PRODUCT
ENVIRONMENTAL PROFILE

- Quick/Entry feature speeds installation by eliminating need for tools, allows you to push stripped or unstripped non-metallic cable into a single gang plastic box without removing knockouts.
- Specially designed drill point rapidly penetrates medium gauge steel studs.
- Screws have combination Hex/Phillips washer heads.
- Quick/Click feature on wall boxes offers fast and dependable installation of devices.
- Can be used for steel, aluminum, or wood studs.
- Molded of high-impact thermoplastic.
- Locator ribs ensure proper alignment on stud and proper offset depth.

SPECIFICATIONS

GENERAL INFO

Size: Deep

Product Series: Slater

Type: Steel Stud Box

Special Features: Quick/Click, Quick/Entry

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
Federal Spec: No
UL Standard: Yes
UN SPSC: 39121308

DIMENSIONS

Depth (US): 3.375"
Height (US): 3.75"
Width (US): 2.25"

TECHNICAL INFORMATION

Material: Steel
Mounting: Captive Mounting Screws
NEMA Configuration Number: OS2

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

