



Powering Business Worldwide

pe.eaton.com

Definite Purpose Control - Contactor

C25ANF140A

UPC:786685115917

Dimensions:

- **Height:** 1.97 IN
- **Length:** 3.19 IN
- **Width:** 2.4 IN

Weight:.5 LB

Warranties:

Specifications:

- **Connection:** Quick
- **Amperage Rating:** 40A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** Compact, single-pole
- **Model:** Contactor
- **Number Of Poles:** Single-pole
- **Resistive Load:** 50A
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25ANF 3D Model Xchange](#)
- [C25ANF AutoCAD 2D Footprint \(mm\)](#)
- [C25ANF AutoCAD 2D Footprint](#)
- [C25ANF 3D Inventor](#)
- [C25ANF 2D Drawing Xchange](#)
- [C25ANF 2D PDF](#)
- [Quick Selector - Definite Purpose Contactors](#)

Certifications:

- UL Recognized
- CSA Certified



Product compliance: No Data

© 2016 Eaton. All rights reserved.