

24244-SC1-NK-NP



24X4X24 Screw Cover Type 1 UL Listed Steel No Knockouts No Paint Cover With Teardrop Slots Mounting Holes In Back

SPECIFICATIONS

Brand Name	Milbank
Type	Screw Cover
Application	Enclosure for Mounting Electrical Equipment
Standard	UL Listed
Number Of Outlet	0
Material	G90 Galvanized Steel
Size	24 In x 4 In x 24 In
Color	Unpainted
Construction	Welded
Knockouts	No Knockouts
Mounting	Wall Mount
NEMA Rating	Type 1
Hinge Type	No Hinge
Top	Plain Top



Door	Cover
Latch	Cover Secured with Plated Screws
Support	Formed and Spot Welded
Height	24 IN
Length	4 IN
Width	24 IN

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

