



\*max overall height

**Measurements:**

<u>Height</u>	<u>Width</u>	
12.00"	4.75"	
<u>Max OAH</u>	<u>Min OAH</u>	
120.00"	14.00"	
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Length</u>
2.20 lb	4.74"	4.74"

**Lamping:**

LED PCB LED	238 Rated Lumens
1 7.5W PCB LED	3000 Color Temperature
7.5 total watt	40,000 Rated Life 80+ CRI

Dimmable : Standard Triac/Lutron® or Leviton® CL

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
4.40 lb	10.63"	3.94"	10.63"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
19.80 lb	11.42"	18.90"	11.42"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
4.0000	845094060246	Yes	

**Finish:**

Polished Chrome PC

**Glass:**

Etched/Bubble 89

**Material:**

Bubble Glass + Steel

**Certification:**

Dry Location

**Additional:**

PCB LED (Included)  
Slope: 120