



BENTLEY FR44505BBZ
BRUSHED BRONZE*

WIDTH:	24.0"
HEIGHT:	25.8"
SHADE:	OFF-WHITE CINNAMON TRIMMED SILK
CANOPY:	5" DIA.
SOCKET:	5-60W CAND
NOTES:	THE UPPER CRYSTALS ARE 10 AND 3/8", USE AT LEAST 11" OF CHAIN IF THEY WANT TO HANG THE UPPER CRYSTALS.
CHAIN:	120.0"
LEADWIRE:	144.0"
CERTIFICATION:	C-US DRY RATED
VOLTAGE:	120V
UPC:	640665905106
INSTALL OPTIONS:	UP, INSTALL ON SLOPED CEILING 90°

AT HINKLEY, WE EMBRACE THE DESIGN PHILOSOPHY THAT YOU CAN MERGE TOGETHER THE LIGHTING, FURNITURE, ART, COLORS AND ACCESSORIES YOU LOVE INTO A BEAUTIFUL ENVIRONMENT THAT DEFINES YOUR OWN PERSONAL STYLE. WE HOPE YOU WILL BE INSPIRED BY OUR COMMITMENT TO KEEP YOUR 'LIFE AGLOW.'

*life*AGLOW®