



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
7.00"	18.00"	4.07"
<u>BP Height</u>	<u>BP Width</u>	
4.75"	18.00"	
<u>Hanging Weight</u>		
3.53 lb		

Lamping:

Incandescent MB Incandescent	2,300 Rated Lumens
2.00 100W MB Incandescent	Color Temperature
200 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
4.23 lb	8.07"	6.89"	20.28"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209801219	Yes	

Finish:

Satin Nickel SN

Glass:

Marble MR

Material:

Aluminum

Certification:

Damp Location
Location

Additional:

MB Incandescent (Not Included)
Lighting Direction: Both