



**Measurements:**

<u>Height</u>	<u>Width</u>
23.50"	26.00"
<u>Hanging Weight</u>	
11.03 lb	

**Lamping:**

Incandescent MB	5,750 Rated Lumens
5.00 60W MB	Color Temperature
300 total watt	2,500 Rated Life
Dimmable : Standard Dimmer	

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
13.89 lb	8.47"	21.46"	26.18"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209085992	Yes	

**Finish:**

Oil Rubbed Bronze OI

**Glass:**

Ice IC

**Material:**

Steel

**Certification:**

Dry Location  
Location

**Additional:**

MB (Not Included)