



*height from center of outlet to the top of the fixture

Measurements:

<u>Height</u>	<u>Width</u>	<u>Length</u>	<u>Extension</u>
18.50"	9.50"	5.00"	6.00"
<u>BP Height</u>	<u>BP Width</u>	<u>HCO</u>	
10.00"	4.50"	6.00000"	
<u>Hanging Weight</u>			
4.40 lb			

Lamping:

Incandescent MB Incandescent 1,150 Rated Lumens
 1.00 100W MB Incandescent Color Temperature
 100 total watt 2,500 Rated Life
 Dimmable : Standard

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
6.00 lb	10.00"	20.47"	11.42"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
26.84 lb	20.87"	21.46"	23.62"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
4.0000	783209100435	Yes	

Finish:

Rust Patina RP

Glass:

Clear CL

Material:

Die Cast Aluminum

Certification:

Wet Location Location

Additional:

MB Incandescent (Not Included)