




PRODUCT DESCRIPTION

Dover Cast is a traditional, Mediterranean style collection from Maxim Lighting International in Bronze finish with Seedy glass.



*height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION : 6.5" W x 9.5" H x 7.5" Ext
 BACK PLATE : 5" W x 6.5" H x 5" HCO
 HANGING WEIGHT : 1.72 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 1 x 60W Incandescent E26 Medium , 60W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Yes

FINISHES OPTION

 Bronze

GLASS

Seedy CD

MATERIAL

Die Cast Aluminum

RATINGS

cETLus
 Wet Location



ADDITIONAL

OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746
EASTERN DISTRIBUTION CENTER
 4200 SHIRLEY DR. | ATLANTA, GA 30336
 P. 626.956.4200 | F. 626.956.4225 | maximlighting.com