

## FM390DAB: 2 - Light Indoor Flushmount



### Dimensions:

**Diameter:** 13"      **Wire:** 8" (color/Black/White)  
**Height:** 4 5/8"      **Mounting Proc.:** Cross Bar  
**Weight:** 5.39 lbs.      **Connection:** Mounted To Box

### Bulbs:

2 - Medium 75w Max. 120v - Not included

### Features:

•

### Material List:

1 Body - - Dark Antique Brass

### Safety Listing:

Safety Listed for Damp Locations / Non-IC

### Instruction Sheets:

Trilingual (English, Spanish, and French) (FM390)  
 Trilingual (English, Spanish, and French) (FM390DAB)

**Collection:** Cadence

**UPC #:** 014817521986

**Finish:** Dark Antique Brass (DAB)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	White Opal Etched	1				4 1/2	12 3/8				

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			2 3/8	13		
Canopy			2 3/8	13		

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship

Individual	FM390DAB	1	014817521986	16.5	16.5	9.75	1.536	7.3	150	Yes
NJ Pallet		40		48	40	71.25	79.167	292		No
NV Pallet		40		48	40	71	78.889	276		No