



## 30 AMP NEMA L630 SINGLE RECEPTACLE, RED

L630RR | [Pass & Seymour](#)

### FEATURES & BENEFITS

Turnlok Receptacle Single 3wire 30amp 250v, Red



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### SPECIFICATIONS

#### GENERAL INFO

Color: Red  
Type: Single Receptacles  
Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CSA Standard: Yes  
CUL Listing No: CSA-C22.2 No. 42  
cULus: Yes  
cURus: No  
Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes

UN SPSC: 39121403

UR: No

#### TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L630

Volts: 250V

Volts (AC): 250

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

