

MINKA-LAVERY®

Item #: 4969-84	UPC Code: 747396068404
Product Family Name: Overland Park	Finish: Brushed Nickel
Category: Chandeliers	Category Type: Chandelier
Certification 4000164	
Patents	
Notes:	



Image File Name:

4969-84--
1378919622.jpg



MEASUREMENTS

Width: 30	Length: 30	Height: 29.25	Extension:
Height Adjustable: Yes	Min Overall Height: 32.50	Max Overall Height: 103.00	Slope: No
Wire Length: 120	Chain Length: 72	Safety Cable Included: No	Net Weight: 23.81
Canopy Width: 5.50	Canopy Height: 0.75	Canopy Length: 5.50	
Backplate Width: 	Backplate Height: 	Center to Top: 	Center to Bottom:

LAMPING

No. of Bulbs: 9	Light Type: A-19, Medium			
Max Bulb Wattage: 100	Socket: E26, Medium			
Dimmable: Yes	Ballast: 	Rated Life Hours: 	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.: 	CRI: 	Initial Lumens: 	Delivered Lumens:

SHADE / GLASS

Description: 	Material: Glass
Part No.: G4961	Quantity: 9
Width: 4.75	Height: 5.75
	Length: 4.75



SHIPPING

Carton Width: 11.500	Carton Height: 29.500	Carton Length: 30.500
Carton Weight: 31.240	Carton Cubic Feet: 5.988	Small Package Shippable: Yes
Master Pack Width: 	Master Pack Height: 	Master Pack Length:
Master Pack Weight: 	Master Cubic Feet: 	Multi-Pack: 1
		Master Pack: 1



ETL Intertek

Yes