



Measurements:

<u>Height</u>	<u>Width</u>
14.00"	14.75"
<u>Max OAH</u>	
14.00"	
<u>Hanging Weight</u>	
4.41 lb	

Lamping:

Incandescent MB Incandescent	2,300 Rated Lumens
2.00 100W MB Incandescent	Color Temperature
200 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
7.19 lb	14.96"	13.78"	14.96"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209584358	Yes	

Finish:

Satin Nickel SN

Glass:

Marble MR

Material:

Steel

Certification:

Dry Location
Location

Additional:

MB Incandescent (Not Included)