



**Measurements:**

<u>Height</u>	<u>Width</u>	<u>Extension</u>
7.00"	21.50"	2.75"
<u>BP Height</u>	<u>BP Width</u>	
4.75"	6.50"	
<u>Hanging Weight</u>		
7.00 lb		

**Lamping:**

Incandescent MB Incandescent	3,450 Rated Lumens
3.00 100W MB Incandescent	Color Temperature
300 total watt	2,500 Rated Life
Dimmable : Standard	

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
9.60 lb	11.00"	10.25"	21.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209054295	Yes	

**Finish:**

Satin Nickel SN

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Damp Location  
Location

**Additional:**

MB Incandescent (Not Included)  
Lighting Direction: Both

