



Specification Sheet

T8 EcoMax[®] U-Bent Rapid Start Fluorescent Lamp

Order Number **37317**




Specifications

Energy Used (Watts).....	32
Domestic Code.....	FB32T8/841/6/ECOMAX
Brightness (Lumens)	2800
Average Rated Hours (3 hrs./Start)	20000
Average Rated Hours (12 hrs./Start)	24000
Life (in years)*	18.3
Light Appearance (Kelvin)	4100
CRI	84
CIE Chromaticity	x.380, y.380
Efficacy (LPW).....	88
Estimated Yearly Energy Cost**	\$3.85
Country of Origin	Mexico


Physical Characteristics

Base	Medium BiPin
MOL.....	22.5"

Lumen Maintenance



Spectral Distribution



Limited Warranty

This lamp is warranted to be free from defects in material and workmanship for 2 years (based on continuous usage 12 hours per day). If the product fails during the warranty period, return defective product to retailer. Warranty terms and conditions of retailer apply. If replacement product is not available at retail store, please return product, original package and receipt to manufacturer at: 12401 McNulty Road, Philadelphia, PA 19154-1029.

TCLP Compliant

* Based on 3 hrs./day
 ** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Contains mercury. For more on clean up and safe disposal, visit epa.gov/CFL.

Call 1-800-999-2226 or visit www.westinghouselighting.com

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee
 ©“Westinghouse” and “You can be sure...if it’s Westinghouse” are all registered trademarks of Westinghouse Electric Corporation

