



Measurements:

<u>Height</u>	<u>Width</u>
6.00"	13.50"
<u>Hanging Weight</u>	
2.20 lb	

Lamping:

Incandescent MB Incandescent	1,344 Rated Lumens
2.00 60W MB Incandescent	Color Temperature
120 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
3.80 lb	14.76"	6.30"	14.76"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209059863	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB Incandescent (Not Included)