



Landscape Lights
T&B Catalog Number:

VGL-01
 04226952410
 Active

UPC Number:
Status:
Description:

100-Watt Glass Globe

Features

Fully threaded globes prevent cross threading assuring a tight seal.

Application

Low maintenance indoor/outdoor lighting where moisture, dirt, dust, corrosion and rough service are problems.

Low-profile fixture design for where low ceiling height presents a light problem

To light cold storage facilities, walkways, bridges, tunnels and security locations.

Used with colored globes as warning, caution or directional lights.

General

Material	Lime Crystal Glass
Globe Material	Lime Crystal Glass
Maximum Wattage	100

Dimension Information

Inner Diameter (inches)	21 1/16
-------------------------	---------

Packaging

T&B Order Multiple	6
T&B Inner Pack	1
Package in Units	6
T&B Sold in UOM	Each
T&B Weight Per UOM	1.08 lbs. Each

Application Support

Product Overview	Available on Website
------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
 E 51152

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com