



Measurements:

| | |
|-----------------------|--------------|
| <u>Height</u> | <u>Width</u> |
| 6.00" | 11.50" |
| <u>Hanging Weight</u> | |
| 2.25 lb | |

Lamping:

| | |
|------------------------------|-------------------|
| Incandescent MB Incandescent | 672 Rated Lumens |
| 1.00 60W MB Incandescent | Color Temperature |
| 60 total watt | 2,500 Rated Life |
| Dimmable : Standard | |

Shipping:

| | | | |
|------------------------|---------------------|----------------------|----------------------|
| <u>Carton Weight</u> | <u>Carton Width</u> | <u>Carton Height</u> | <u>Carton Length</u> |
| 3.50 lb | 13.00" | 6.42" | 13.00" |
| <u>Master Pack Qty</u> | <u>UPC</u> | <u>UPS</u> | |
| 1.0000 | 783209059856 | Yes | |

Finish:

Oil Rubbed Bronze OI

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB Incandescent (Not Included)