

# MINKA-LAVERY®

Item # <b>2933-84-L</b>	UPC Code: <b>747396092126</b>
Product Family Name: <b>Celice Bath</b>	Finish: <b>Brushed Nickel</b>
Category: <b>BATH</b>	Category Type: <b>Bath</b>
Certification <b>4010381</b>	
Patents:	
Notes:	




Image File Name: 2933-84-L.jpg



## MEASUREMENTS

Width: <b>24</b>	Length: <b>6</b>	Height: <b>6</b>	Extension: <b>1.5</b>
Height Adjustable: Min Overall Height: <b>No</b>		Max Overall Height: <b>No</b>	Slope: <b>No</b>
Wire Length: <b>7"</b>	Chain Length:	Safety Cable Included: <b>No</b>	Net Weight: <b>4.45</b>
Canopy Width: <b>23.75</b>	Canopy Height: <b>5.75</b>	Canopy Length:	Center to Bottom: <b>3.0</b>
Backplate Width:	Backplate Height:	Center to Top: <b>3.0</b>	

## LAMPING

No. of Bulbs: <b>1</b>	Light Type: <b>L-MD-L36724-37W</b>			
Max Bulb Wattage: <b>37</b>	Socket: <b>LED</b>			
Dimmable: <b>Yes</b>	Ballast:	Rated Life Hours: <b>30000</b>	Photocell Included: <b>No</b>	Bulb/LED Included: <b>Y</b>
Bulb/LED Included: <b>Yes</b>	Color Temp.: <b>3000</b>	CRI: <b>83</b>	Initial Lumens: <b>4209.13</b>	Delivered Lumens: <b>1369.93</b>

## SHADE / GLASS

Description: <b>Etched White</b>	Material: <b>Glass</b>
Part No.: <b>G2933</b>	Quantity: <b>1</b>
Width: <b>23.0</b>	Height: <b>5.13</b>
	Length: <b>0.13</b>



## SHIPPING

Carton Width: <b>8.25</b>	Carton Height: <b>4.0</b>	Carton Length: <b>27.75</b>
Carton Weight: <b>5.544</b>	Carton Cubic Feet: <b>0.53</b>	Small Package Shippable: <b>Yes</b>
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: <b>1</b>

**LED**



**ADA  
Compliant**



**Damp  
Location**



**ETL  
Intertek**

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.