

## Two Light Vanity 5852CM



ITEM NUMBER	5852CM
BRAND	Hinkley Lighting
MATERIAL	Metal
GLASS	Etched
HEIGHT	7.8"
WIDTH	16.0"
VOLTAGE	120v
WATTAGE	2-100w Incan. OR 2-17w LED Med.
CERTIFICATION	C-US Damp Rated
EXTENSION	7.5"
TOP TO OUTLET	5.3"
BACK PLATE	6.5"W X 4.5"H

### FEATURES AND BENEFITS

- Fixture can be mounted either up or down
- Suitable for use in damp (interior moist and outdoor no direct rain or sprinkler) locations as defined by NEC and CEC. Meets United States UL Underwriters Laboratories & CSA Canadian Standards Association Product Safety Standards
- For complete warranty information visit [\(hyperlink\)](#)
- 15 year finish warranty
- Lifetime warranty on electrical wiring and components
- Classic, elegant lines and timeless details enhance a traditional space
- Sparkling chrome with reflective finish

FINISH Chrome

AT HINKLEY, WE EMBRACE THE DESIGN PHILOSOPHY THAT YOU CAN MERGE TOGETHER THE LIGHTING, FURNITURE, ART, COLORS AND ACCESSORIES YOU LOVE INTO A BEAUTIFUL ENVIRONMENT THAT DEFINES YOUR OWN PERSONAL STYLE. WE HOPE YOU WILL BE INSPIRED BY OUR COMMITMENT TO KEEP YOUR 'LIFE AGLOW.'

*life*AGLOW®