



Item #: <b>F620-BN</b>	UPC Code: 706411033766
Product Family Name: <b>Bolo™</b>	Finish: Brushed Nickel
Category: <b>Interior Fan</b>	Category Type: Ceiling Fan
Certification <b>E75795</b>	
Patents	
Notes:	

Image File Name:  
F620-BN\_0.jpg



## MEASUREMENTS

Blade Finish:	Reversible Blades:		
	<b>No</b>		
Blade Material:	Slope:		
<b>Plywood Construction</b>	<b>No</b>		
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
<b>52</b>	<b>5</b>	<b>14 degrees</b>	<b>24.98</b>
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
<b>3.5</b>	<b>.75</b>	<b>6</b>	<b>.75</b>
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
<b>20.00</b>	<b>11.38</b>	<b>80</b>	<b>172x17mm</b>

	Low:	Low/Med:	Medium:	Med/High:	High:
<b>RPM:</b>	72		111		168
<b>Amps:</b>	0.36		0.50		0.62
<b>Watts:</b>	16.000		35.000		74.000
<b>CFM:</b>	2185.43		3716.63		5712.25
<b>CFM/Watts:</b>	136.59		106.19		77.19



## FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
<b>No</b>	<b>Yes</b>	<b>Yes</b>
	Included Remote Control:	Included Wall Control:
	<b>RCS213</b>	
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
		<b>WCS213</b>

## LAMPING

No. of Bulbs:	Light Type:			
<b>3</b>	<b>B10.5 Candelabra</b>			
Max Bulb Wattage:	Socket:			
<b>60</b>	<b>E12</b>			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
<b>Yes</b>	<b>Yes</b>			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
<b>Yes</b>				

## GLASS

Description:	Material:
	<b>Glass</b>
Part No.:	Quantity:
<b>GF620-2</b>	<b>1</b>
Width:	Height:
	Length:



## SHIPPING

Carton Width:	Carton Height:	Carton Length:	
<b>15.000</b>	<b>11.380</b>	<b>28.380</b>	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
<b>29.480</b>	<b>2.804</b>	<b>Yes</b>	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
		<b>1</b>	<b>1</b>



Title 17

Yes



UL Listed

Yes