



Measurements:

<u>Height</u>	<u>Width</u>
18.25"	19.00"
<u>Max OAH</u>	
17.70"	
<u>Hanging Weight</u>	
8.27 lb	

Lamping:

Incandescent MB Incandescent	3,450 Rated Lumens
3.00 100W MB Incandescent	Color Temperature
300 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
8.60 lb	11.81"	14.96"	18.70"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209025820	Yes	

Finish:

Satin Nickel SN

Glass:

Ice IC

Material:

Steel

Certification:

Dry Location
Location

Additional:

MB Incandescent (Not Included)