

Specification Sheet

Eco-PAR PLUS Halogen PAR38 Reflector Incandescent Lamp

Order Number **36852**

Specifications

| | |
|---------------------------------------|-----------------------|
| Energy Used (Watts)..... | 38 |
| Incandescent Equivalent Wattage | 45 |
| Domestic Code..... | 38PAR38/H/FL/ECO/PLUS |
| Volts..... | 120 |
| Candle Power..... | 1000 |
| Beam Spread | 30° |
| Beam Type..... | Flood |
| Filament Type | CC8 |
| Light Appearance (Kelvin) | 2750 |
| Efficacy (LPW)..... | 14 |
| Brightness (Lumens) | 550 |
| Average Rated Hours | 2000 |
| Life (in years)* | 1.8 |
| Dimmable..... | Yes |
| Estimated Yearly Energy Cost** | \$4.58 |
| Country of Origin..... | China |



Physical Characteristics

| | |
|-----------|--------|
| Base..... | Medium |
| MOL..... | 5 3/8" |

* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee
 ®“Westinghouse” and “You can be sure...if it’s Westinghouse”are all registered trademarks of Westinghouse Electric Corporation

