

Eaton main circuit breaker

3MCB600R

UPC:786849053253

Dimensions:

- **Height:** 14.5 IN
- **Length:** 48.75 IN
- **Width:** 23.75 IN

Weight:112 LB

Notes:If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil]. Add CL to end of catalog number for compression lug pads (includes lug pads for lines and neutral).

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 600A
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Bottom
- **Interrupt Rating:** 65 kAIC
- **Main Circuit Breaker:** LD
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Voltage Rating:** 120/208V
- **Wire Size:** (2) 400-500 kcmil

Supporting documents:

- [Dimensional Drawing - METERING DIMENSIONS DWG. FOR METER CTR. BREAKER MAINS - 400-600A](#)
- [Eatons Volume 1-Residential and Light Commercial](#)



- [Eaton Specification Sheet - 3MCB600R](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.