

Item #: P4400-084	UPC Code: 870540001832
Product Family Name: Save Your Marriage™	Finish: Brushed Nickel
Category: Wall Mount	Category Type: Wall Lamp
Certification 4000165	
Patents	
Notes: Dual Dimmer Switches Convertible to Pin-Up; Adjusts To E. 22 1/4" Max. Adjusts width to 49 1/2"	



Image File Name:
P4400-084--
1391716027.jpg



MEASUREMENTS

Width: 16	Length: 8.5	Height: 7	Extension: 17.25
Height Adjustable: Yes	Min Overall Height: 8.50	Max Overall Height: 17.25	Slope: No
Wire Length: 96	Chain Length: 11.88	Safety Cable Included: No	Net Weight: 5.95
Canopy Width: 11.88	Canopy Height: 4.38	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 2	Light Type: Mr-16(Gu5.3,12v)			
Max Bulb Wattage: 50	Socket: Gy6/35/Gu5.3/G4,2-Pin			
Dimmable: Yes	Ballast: Yes	Rated Life Hours: Yes	Photocell Included: Yes	Lamps Included: Yes
Lamp Included: Yes	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Steel
Part No.:	Quantity: 2
Width: 2.38	Height: 4.13
	Length:



SHIPPING

Carton Width: 4.500	Carton Height: 20.630	Carton Length: 18.000	
Carton Weight: 8.470	Carton Cubic Feet: 0.967	Small Package Shippable: Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1	Master Pack: 1



ETL Intertek

Yes