




**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™



FISHTAPE,STEEL-50' 5-PACK

Steel Fish Tape - 50' x 1/8 (15.2 m x 3.2 mm)

Cat No: 438-5H

UPC No: 783310075004

### Description

---

- Oil-tempered spring steel for excellent fishing performance
- Dirt-free tape finish keeps hands cleaner during use
- Advanced comfort handle grip reduces fatigue
- Superior rapid tape pay-out and rewind
- Smaller fish eye with offset bend for improved fishing ability
- Improved low profile tip for easy fishing through all sizes of conduit
- Viewing port gives visibility to remaining tape and ability to remove jobsite debris quickly
- Rugged case design improves drop impact capability
- Flared case with grip ridges for no slip handling
- Available in 50 FT (15.2 m), 65 FT (19.8 m), 125 FT (38.1 m) and 240 FT (73.2 m) lengths
- 1/8 IN, 1/4 IN and flat steel profiles to accommodate different fishing situations

### Specifications

---

- Accessory : R438B Swivel Ball Head for use on 1/8 IN Steel Fish Tapes, R438-BM Ball Tip Male Half, 439-1 12 IN (305 mm) Flexible Fish Tape Leader, 439-2 12 IN (305 MM) SPEED FLEX Leader (solder joints)
- Application : For Excellent Fishing Performance
- Length : 50.000 FT (15.200 M)
- Material : Steel
- Replacement Part :
  - 10051 8-1/2 IN Case/Handle Replacement Kit
  - 10052 12 IN Case/Handle Replacement Kit
- Sub Brand : MagnumPRO
- Tensile Strength : 400.000 LB (1.700 KN) Maximum Design Strength
- Weight : 2.800 LB (1.300 KG)
- Width : 1/8 IN (3.200 MM)