


DIMENSIONAL INFORMATION

HEIGHT	10"
LENGTH	-
ADA COMPLIANT	No
CHAIN LENGTH	-
STEM KIT	N/A
CANOPY/BACKPLATE	5.25"
WIDTH	16"
DIAMETER	-
MINIMUM HEIGHT	-
MAXIMUM HEIGHT	-
EXTENSION	7"

LAMPING INFORMATION

(2) 100 WATT MAX 120 VAC	
BULB INCLUDED	No
SOCKET TYPE	E26 Medium Base - A19 Bulb

SHADE INFORMATION

SHADE TOP	2.625"
SHADE BOTTOM	6"
SHADE HEIGHT	5.25"
SHADE ATTACHMENT	Socket Ring
SHADE MATERIAL	GLASS
SHADE COLOR	Opal/Matte

SHIPPING INFORMATION

CARTON LENGTH	24"
CARTON WIDTH	12"
CARTON HEIGHT	9"
GROSS WEIGHT	7 lbs.
SHIPPING METHOD	UPS
QUANTITY PER CARTON	1

OTHER INFORMATION

UL RATING	Damp
-----------	------

AVAILABLE FINISHES

POLISHED NICKEL (PN), SATIN NICKEL (SN)

JOB/LOCATION
QUANTITY
NOTES