



S5011

50A19/F/12V
50 watt A19 Incandescent; Frost; 1500 average rated hours;
540 lumens; Medium base; 12 volts

Features

- General Service Incandescent
- Household or Commercial use
- Long Life
- 12 volt



S5011

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S5011	045923050114	50	A19	Medium	E26	50A19/F/12V	12
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost	4 1/8"	2.38"	C-6	540	1500	120/6	Box
Dimmable/Non-Dimmable			CEC Status			RoHS Compliant	
Dimmable			Lawful for sale in California			Yes	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

