

Project Name

Location

Prepared By



SATCO S7291

15A19/E26/2700K/120V/1PK

Notes

General

Status	Active
Watts	15
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
CCT (Kelvin)	2700
Temperature	Warm White
CRI	82
Lumens	800
Beam Spread	360
Hours Rated	10000
Lamp Type	A-Type
Technology	Compact Fluorescent

Electrical

Hg Content	1.6
THD	<150

Physical

MOL	4.63
MOD	2.28

Additional Information

Warranty	2 or 3 Year Limited - CFL
----------	---------------------------

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	CFL_Self_Ballasted_Lamp