



\*max overall height

**Measurements:**

<u>Height</u>	<u>Width</u>
14.50"	24.50"
<u>Max OAH</u>	
56.50"	
<u>Hanging Weight</u>	
22.97 lb	

**Lamping:**

Incandescent MB	2,300 Rated Lumens
2.00 60W MB	Color Temperature
120 total watt	2,500 Rated Life
Dimmable : Standard	

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
34.94 lb	27.50"	20.50"	27.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209083875	Yes	

**Finish:**

Umber Bronze UB

**Glass:**

Dusty White DW

**Material:**

Steel

**Certification:**

Dry Location  
ADA

**Additional:**

MB (Not Included)