



\*max overall height

**Measurements:**

Height

11.00"

Max OAH

56.00"

Hanging Weight

3.70 lb

Width

7.00"

**Lamping:**

Incandescent MB

1.00 60W MB

60 total watt

Dimmable : Standard

1,150 Rated Lumens

Color Temperature

2,500 Rated Life

**Shipping:**

Carton Weight

6.00 lb

Carton Width

14.38"

Carton Height

9.13"

Carton Length

14.63"

Master Pack Qty

1.0000

UPC

783209084056

UPS

Yes

**Finish:**

Umber Bronze UB

**Glass:**

Dusty White DW

**Material:**

Steel

**Certification:**

Dry Location

ADA

**Additional:**

MB (Not Included)

Slope: 120