


DIMENSIONAL INFORMATION

HEIGHT	11"
LENGTH	-
ADA COMPLIANT	No
CHAIN LENGTH	-
STEM KIT	3" 6" 12" 2-18"
CANOPY/BACKPLATE	6"
WIDTH	-
DIAMETER	7"
MINIMUM HEIGHT	14"
MAXIMUM HEIGHT	68"
EXTENSION	-

LAMPING INFORMATION

(1) 100 WATT MAX 120 VAC	
BULB INCLUDED	No
SOCKET TYPE	E26 Medium Base - A19 Bulb

SHADE INFORMATION

SHADE TOP	1.875"
SHADE BOTTOM	6.75"
SHADE HEIGHT	5.125"
SHADE ATTACHMENT	Socket Ring
SHADE MATERIAL	GLASS
SHADE COLOR	Opal/Glossy

SHIPPING INFORMATION

CARTON LENGTH	21"
CARTON WIDTH	9"
CARTON HEIGHT	9"
GROSS WEIGHT	6 lbs.
SHIPPING METHOD	UPS
QUANTITY PER CARTON	1

OTHER INFORMATION

UL RATING	Damp
-----------	------

AVAILABLE FINISHES

AGED BRASS (AGB), HISTORIC BRONZE (HB), POLISHED NICKEL (PN), SATIN NICKEL (SN)

JOB/LOCATION
QUANTITY
NOTES