



Item # F524-ORB
 Product Family Name: Roto
 Category: INTERIOR FAN
 Certification: 4000048
 Patents: U.S. Patent(s): D750,221; Add'l U.S. Patent(s) Pending
 Notes:

UPC Code: 706411045479
 Finish: Oil Rubbed Bronze
 Category Type: Ceiling Fan



Image File Name: F524-ORB.jpg



MEASUREMENTS

Blade Finish:				Reversible Blades:	No
Blade Material:				Slope:	Yes
ABS Construction				Hanging Weight:	10.36
Blade Sweep:	No. of Blades:	Blade Pitch:			
52"	3	22	Downrod 1 Outside Dia:	Downrod 2 Outside Dia:	
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:			
6	0.75				
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade (Dim B)	Lead Wire:	Motor Size:		
9.25	7.0	80	153x15mm		

	Low	Low/Med.	Medium	Med/High	High
RPM:	74		127		212
Amps:	0.17		0.26		0.44
Watts:	7.5		18.3		51.3
CFM:	2060.0		3519.0		5816.0
CFM/Watts:	274.67		192.3		113.37

LAMPING

No. of Bulbs:	Light Type:			
0				
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight:
No	No			No
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

GLASS

Description:	Material:
Part No.:	Quantity:
Width:	Height:
	Length:



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
Reversible:	Included Remote Control:	Included Wall Control:
No		WC105-WH
	Compatible Remote Control(s):	Compatible Wall Control(s):
	RCS223	WCS223



SHIPPING

Carton Width:	Carton Height:	Carton Length:
9.5	9.0	24.75
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
12.76	1.225	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1



ETL
Intertek

WARNING: Handling this product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. Wash hands with soap and water after installing, handling, cleaning or otherwise touching this product. For more information go to: www.P65Warnings.ca.gov.

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.