



# S3002

60G40/W  
60 watt G40 Incandescent; Gloss White; 4000 average rated hours; 550 lumens; Medium base; 120 volts

### Features

- Decorative incandescent
- Long Life
- Brass Base



S3002

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3002	045923030024	60	G40	Medium	E26	60G40/W	120
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Gloss White	6-3/4"	5.00"	C-9	550	4000	24/6	Box
Dimmable/Non-Dimmable			CEC Status		RoHS Compliant		
Dimmable			Lawful for sale in California		Yes		



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

