

Renew Patio 52" Fan Tannery Bronze™

339515TZP (Tannery Bronze Powder Coat)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____

**Airflow**

CFM (High)	4870
CFM (Low)	1516
RPM (High)	202
RPM (Low)	174

Certifications/Qualifications

Location Rating	CSA UL Listed Wet
Title 20 Compliant	Yes
	www.kichler.com/warranty

Dimensions

Base Backplate	6.00 DIA
Downrod 1	1.00 OD X 4.00"
Downrod 2 - Measurement A	9.25"
Downrod 2 - Measurement B	6.75"
Downrod 2 - Measurement C	11.75"
Downrod 2	FLUSH MOUNT"
Weight	23.10 LBS
Height	12.25"
Width	52.00"

Electrical

Amps (High)	0.57
Amps (Low)	0.23
Motor Size	153MM X 15MM
Motor Type	AC

Mounting/Installation

Dual Mount	Yes
Minimum Distance from Fan to Floor	7 feet
Interior/Exterior	Exterior
Lead Wire Length	78
Low Ceiling Adaptable	Yes, Dual Mount Included
Mounting Weight	23.10 LBS

Primary Lamping

Downlight Option	Optional
Watts (High)	67
Watts (Low)	10

Product/Ordering Information

SKU	339515TZP
Finish	Bronze
Style	Traditional
UPC	783927416900

Specifications

Blade Finish 1	BROWN
Blade Finish 2	NON-REVERSIBLE
Blade Material	ABS
Blade Pitch	12
Blades Included	Yes
Blade Sweep	52
Material	STEEL
Max Stem Tilt	22 Degrees
Number of Blades	5

Additional Finishes



Satin Black



Tannery Bronze Powder Coat



White

Kichler

7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010
Toll free: 866.558.5706 or kichler.com

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

KICHLER®