



GE
Lighting

94382 - Remote 4ft LED Plastic Tubes

LED21T8/4/840

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ Each LED tube is operated by a GE Lighttech™ driver.
- ☞ 66% longer life than LFL (50,000 vs. 30,000 hours)
- ☞ Instant on light
- ☞ NSF Rated for food application (shatter resistant)
- ☞ Easy disposal, non-hazardous waste
- ☞ UL Listed
- ☞ DLC Listed

Product Photo



CAUTIONS & WARNINGS

Caution

Risk of electric shock

Suitable for damp locations

Not intended for use with emergency exit fixtures or emergency exit lights

GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	50000 h
LED Tube Type	Plastic
10 Digit U	4316894382
Lamp Count	1
Life in Years	45.7 yr
Replacement Watts	0 W
Requested Structure	Case Pack
Estimated Energy Cost per Year	2.17
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	2750 lm
Color Rendering Index-CRI	80
Color Temperature	4000 K

PRODUCT INFORMATION

Product Code	94382
Description	LED21T8/4/840
Alternative Unit Of Measure	CASE
Standard Package Quantity	10
Ean UPC	043168943826
Standard Package GTIN	10043168943823
No Of Items Per Sales Unit	
No Of Items Per Standard Package	10
Sales Unit	Case
UCC	043168943826
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168943826
Standard Package GTIN	00043168943826
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168943826

DIMENSIONS

Bulb Max Overall Length-MOL	48.0 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	18 W
---------------------	------