



### 4738-98: Four Light Wall / Bath



**Collection:** Center Stage

Four Light Brushed Stainless Bath Bracket that can be Mounted Horizontal or Vertical. The Bulbs are spaced at 6in apart.

Four-bulb bar light fixture with stainless finish. Sockets spaced on 6" centers.

**UPC #:**785652473883

**Finish:** Brushed Stainless (98)

### Dimensions:

<b>Width:</b>	24"	<b>Extends:</b>	2 1/4"
<b>Height:</b>	4 1/4"	<b>Wire:</b>	6 1/2"
<b>Weight:</b>	2.2 lbs.	<b>Mounting Proc.:</b>	Wall / Bath
		<b>Connection:</b>	Mounted To Box

### Bulbs:

4 - Medium G25 100w Max. 120v - Not included

### Features:

- Fixture may be mounted horizontal or vertical
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

1 Body - Steel - Brushed Stainless

### Safety Listing:

Safety Listed for Damp Locations

### Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-107FB)

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate					2 1/8	

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	4738-98	1	785652473883	25	5	2.5	0.181	2.4	85	Yes
Master Pack	4738-98	6	10785652473880	25	10	7.5	1.085	14.6	85	Yes
NJ Pallet		288		48	40	65	72.222	700.8		No
NV Pallet		294		48	40	65	72.222	716		No