



## Specification Sheet

# Low Voltage A19 General Purpose Incandescent Lamp

Order Number **03422**

### Specifications

Energy Used (Watts).....	25
Domestic Code.....	25A/F/12V
Volts.....	12
Brightness (Lumens) .....	250
Average Rated Hours .....	2500
Life (in years)* .....	2.3
Dimmable.....	Yes
Filament Type .....	C6
Light Center Length (LCL) .....	2 3/4"
Estimated Yearly Energy Cost** .....	\$3.01
Country of Origin.....	China



### Physical Characteristics

Finish .....	Frost
Base .....	Medium
MOL.....	4 1/8"

\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee  
©, WESTINGHOUSE and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

