



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Series C, F-frame Molded Case Circuit Breaker

EHD2070

UPC:786679317495

### Dimensions:

- **Height:** 6 IN
- **Length:** 3.38 IN
- **Width:** 2.75 IN

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 70A
- **Number Of Poles:** Two-pole
- **Frame Size:** F-frame
- **Maximum Voltage:** 14 kAIC at 480V
- **Series:** Series C
- **Trip Type:** Thermal magnetic

### Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [EHD2 2D Drawing Xchange](#)
- [EHD2 2D PDF](#)
- [EHD2 3D Model Xchange](#)
- [Counterfeit and Gray Market Awareness Guide](#)
- [MOEM MCCB Product Selection Guide](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers](#)
- [Types EHD and FDB 10 Amperes AB DE-ION Circuit Breakers](#)
- [F-Frame 310+ Molded-case circuit breakers 15-](#)



225A

- F-frame Molded Case Circuit Breaker Drawing
- EHD2 3D Inventor

**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.