



Powering Business Worldwide

pe.eaton.com

Fuse Terminal Blocks for 6.3 x 32 mm (1/4 in x 1-1/4 in) fuse

XBUK10FBCN

UPC:782116925643

Dimensions:

- Height: X
- Length: X
- Width: X

Warranties:

- 1 year

Specifications:

- **Type:** Screw Connection Fuse Terminal Blocks, XBUK10FBC
- **Amperage Rating:** IEC 10A, UL 20A
- **Voltage Rating:** IEC 800V, UL 300V
- **Maximum Wire Size:** 6 AWG/16 mm²
- **Quantity:** 50
- **Used With:** 6.3 x 32 mm
- **Wire Size:** #20-4 AWG
- **Color:** Black

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUK10FBCN](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



