



GE  
Lighting

68855 - F32T8/XL/SPX35E2

F32T8/XL/SPX35E2

### Product Photo



#### GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.95 mg
Mercury-Picogram per mean lm hr	26.6
Rated Life Instant Start-Hrs	25000 h @ 3 h 36000 h @ 12 h
Rated Life Rapid Start - Hrs	40000 h @ 3 h 45000 h @ 12 h
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Sodalime glass
Rated Life Hours-nominal	40000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

#### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2770 lm
Nominal Initial Lumen per Watt	91
Initial Lumens-nominal	2925 lm
Color Rendering Index-CRI	85
Color Temperature	3500 K

#### PRODUCT INFORMATION

Product Code	68855
Description	F32T8/XL/SPX35E2
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168688550
Standard Package GTIN	10043168688557
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168688550

#### DIMENSIONS

Diameter	1.0 in
Nominal Length	48.0 in

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	32 W
---------------------	------