

2 Light Flush Mount Ceiling Light | Brushed Nickel

8654NI (Brushed Nickel)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Dimensions

Height	5.50"
Width	13.25"

Ordering Information

Product ID	8654NI
Finish	Brushed Nickel
Available Finishes	NI, SC, TZ

Dimensions

Base Backplate	13.25 DIA
Weight	3.00 LBS

Specifications

Material	Steel
Glass Description	Satin Etched

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	2
Max or Nominal Watt	60W
Socket Wire	105
Socket Type	Medium
Lamp Type	A19

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	13-15W		

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.