



Powering Business Worldwide

pe.eaton.com

Eaton Series G complete molded case circuit breaker

EGB3020FFG

UPC:782116131303

Dimensions:

- **Height:** 5.5 IN
- **Length:** 2.99 IN
- **Width:** 3 IN

Weight:3 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 20A
- **Interrupt Rating:** 25 kAIC at 240 Vac, 18 kAIC at 480 Vac
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600Y/347 Vac
- **Trip Type:** Fixed thermal, fixed magnetic
- **Circuit Breaker Type:** EG
- **Frame Size:** EG-frame
- **Series:** Series G
- **Terminals:** Line and load
- **Frequency Rating:** 50/60 Hz

Supporting documents:

- [Application of Tap Rules to Molded Case Breaker Terminals](#)
- [Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)
- [StrandAble terminals product aid](#)
- [Series G MCCB quick selector](#)



- [Current limiting molded case circuit breaker module for series G, JG and CL](#)
- [Comprehensive circuit protection for control panel applications](#)
- [Circuit breaker motor operators product aid](#)
- [Current limiting molded case circuit breaker module product aid](#)
- [Plug-in adapters for molded case circuit breakers product aid](#)
- [High performance operating handles for Series G circuit breakers product aid](#)
- [Power metering and monitoring with Modbus RTU product aid](#)
- [Molded case circuit breakers providing higher levels of selective coordination product aid](#)
- [Motor protection circuit breakers product aid](#)
- [MOEM MCCB Product Selection Guide](#)
- [Series G Molded Case Circuit Breakers - Quick Selector](#)
- [Multi-wire lugs product aid](#)
- [Molded case circuit breakers](#)
- [Eaton's Volume 4-Circuit Protection](#)
- [EG-frame Molded Case Circuit Breaker Drawing](#)
- [Breaker service centers](#)
- [MOEM MCCB product selection guide](#)
- [NG and ND-Frame molded case circuit breakers](#)
- [EG-Frame Circuit Breaker 15-160 Amperes Technical Data](#)
- [Eaton Series G type EGB, EGE, EGS, EGH, EGC, and EGK circuit breakers](#)

Certifications:

- [UL Listed](#)
- [CSA Certified](#)
- [IEC Rated](#)

Product compliance:

- [CE Marked](#)