

L100

109 CFM High Capacity Ceiling Mount Ventilation Fan, 0.9 Sones, 120V

Overall rating

[Read 1 review](#) | [Write a review](#)

Product Q&A 8 questions | 8 answers
[Read all Q&A](#)

- [Spec Sheet](#)
- [Tools & Resources](#)
- [Installation Guide](#)
- [Where To Buy](#)
- [Product Catalogs](#)
- [Shop for Parts](#)
- [Print](#)



1 Additional Image



Overview	Dwelling Unit Ventilation Selector	Specifications	Accessories	Reviews	Answers
--------------------------	--	--------------------------------	-----------------------------	-------------------------	-------------------------

Broan high capacity fans are an exceptionally quiet solution to continuous ventilation. With their heavy-duty motors, high capacity fans are an ideal solution for conference rooms, public restrooms and other areas in commercial buildings that require ongoing ventilation. Low-vibration and lo-profile, they work quietly without getting noticed.

- 109 CFM 0.9 Sones. (AMCA)
- 120V, 1.1 amps
- 6" round duct connector
- Low profile, white polymeric grille
- Single, impact-resistant centrifugal blower wheel
- 20 gauge galvanized steel housing
- Can be ducted horizontally or vertically. In-line ducting available with separate adapter
- UL Listed for use over tubs and showers with a GFCI circuit; so you can capture the steam before it spreads throughout the room by locating your fan exactly where you need it the most
- Use Broan Electronic Variable Speed Control to adjust blower speed and sound level (available separately)