



Image File Name:
F524-WHF--
1509647399.jpg

Item #: F524-WHF	UPC Code: 706411045462
Product Family Name:	Finish: Flat White
Category: Interior Fan	Category Type: Ceiling Fan
Certification 4000048	
Patents U.S. Patent(s): D750,221; Add'l U.S. Patent(s): Pending	
Notes:	



MEASUREMENTS

Blade Finish:	Reversible Blades:		No
Blade Material: ABS Construction	Slope:		No
Blade Sweep: 52	No. of Blades: 3	Blade Pitch: 22	Hanging Weight: 10.36
Downrod 1: 6	Downrod 1 Outside Dia: 0.75	Downrod 2: 6	Downrod 2 Outside Dia: 0.75
Ceiling to Lowest Point: (Dim A) 9.25	Ceiling to Blade: (Dim B) 7.00	Lead Wire: 80	Motor Size: 153x15mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	74		127		212
Amps:	0.17		0.26		0.44
Watts:	7.500		18.300		51.300
CFM:	2060.00		3519.00		5816.00
CFM/Watts	274.67		192.30		113.37



FAN CONTROLS

Pull Chain Control: No	Works with Remote Control: Yes	Works with Wall Control: Yes
	Included Remote Control:	Included Wall Control: WC105-WH
	Compatible Remote Control[s]: RCS223	Compatible Wall Control[s]: WCS223

LAMPING

No. of Bulbs:	Light Type:		
Max Bulb Wattage:	Socket:		
Light Kit: No	Dimmable: No	Ballast:	Rated Life Hours: Uplight
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens: Delivered Lumens:

GLASS

Description:	Material:
Part No.:	Quantity:
Width:	Height:
	Length:



SHIPPING

Carton Width: 9.500	Carton Height: 9.000	Carton Length: 24.750
Carton Weight: 12.760	Carton Cubit Feet: 1.225	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



ENERGY
STAR
Yes



ETL Intertek

Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties