



Call Us: [718.259.6100](tel:718.259.6100) (tel:718.259.6100) or [800.626.1223](tel:800.626.1223) (tel:800.626.1223)


RIGID-IMC FITTINGS

Malleable Iron Threaded Conduit Bodies

[Download
Specification Sheet
\(https://www.sepco-
usa.com/wp-
content/uploads/2017/03/page_033.pdf\)](https://www.sepco-usa.com/wp-content/uploads/2017/03/page_033.pdf)



[Print](#)



LB1

Trade Size	1/2"
Dim A	4.688
Dim B	1.313
Dim C	2.063
MAX WIRE SIZE	N/A
VOL. CU.IN.	4.50
Unit Pack	10
Master Pack	50
Lbs. / 100 Pcs.	71
UPC	40011
	B50-M, LB-
	61, LB50M,
	LB50M,
Competitor	LBM-50,
Part Number	LB-50,
	LB17, LB17,

LB50M,**LB1M****APPLICATION FEATURES**

To provide access to conductors for pulling splicing, and maintenance. Threaded for rigid conduit and IMC.

Tapered threaded hubs (NPT)

Flat back design for easy mounting close to walls

Suitable for use in concrete

STANDARD MATERIALS STANDARD FINISH

Malleable Iron Zinc Plated

OPTIONAL FINISH UL LISTED

For additional corrosion protection, specify Hot Dipped Galvanized.



Add suffix 'G' to Malleable Iron catalog number.

Example LB1G. For

more information

9/12/2019

Buy Malleable Iron Threaded Conduit Bodies - SEPCO USA

more information,

see page

11.
