



S3842

40G16 1/2/W
40 watt G16 1/2 Incandescent; Gloss White; 1500 average
rated hours; 330 lumens; Medium base; 120 volts

Features

- Decorative incandescent
- Long Life
- Brass Base



S3842

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3842	045923038426	40	G16 1/2	Medium	E26	40G16 1/2/W	120
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Gloss White	3-1/4"	2.06"	CC-2V	330	1500	500/25	Box
Dimmable/Non-Dimmable		CEC Status			RoHS Compliant		
Dimmable		Exempt - Not a general service lamp			Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

