



Product Info

Brand: fiberglassBOX

UPC: 85339104193

UNSPSC: 39121316

Carton Weight: 28 lbs

Country of Origin: United States of America

Color: Off white

Material: Fiberglass reinforced polyester

Additional Materials: Galvanized steel brackets and plated carbon steel fasteners, Polyvinyl chloride clamps

Box Diameter: 4

9350-HFK

4" dia. round fixture support box for use with nonmetallic sheathed cable

Carton Quantity: 50

Closure Type:

Mounting Description: Nail-on backside HN hanger bracket for adjusting to additional wall/ceiling substrate

Box Type: Ceiling - Fixture

Box Features: "HF" bracket, Speed "K" nonmetallic clamps

Installation Type: New Work

Width: 4 in

Depth: 2-7/16 in

Volume: 22.5 cu in

Fixture Rating: 50lbs

Features:

Machine tapped fixture holes, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures, Speed "K" Clamps factory installed

Application:

New work residential construction 2 HR fire resistive walls and ceilings (50 lbs. fixture support)

Box Diameter: 4

Standards:

ANSI / UL 514C: [File No. E30594](#)



LISTED

Fire Classification:

Fire Test of Building Construction Materials

ANSI / UL 263: [File No. CEYY.R9379](#) (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 ½ inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)
