



PASS & SEYMOUR® UL Fed Spec USB Chargers 15 & 20A, 125V

TR5262USB, TR5362USB

Charge ahead with the UL Fed Spec Grade USB duplex receptacle.

Pass & Seymour® Fed Spec Tamper-Resistant Duplex Receptacles with USB Charging capabilities are designed with strength and durability in mind. They were designed for the commercial market, and are capable of withstanding heavy use due to their UL Federal Specification certification. This product features an improved overall 3.1A USB charging capability, auto-ground clips, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The screw-pressure-plate back wiring makes installation fast and easy.



FEATURES & BENEFITS

Overall 3.1A USB charging capability

Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices

AC receptacles available in 15 and 20A, 125V

AC receptacles are tamper-resistant as standard - patented shutter system prevents improper insertion of foreign objects



TR5262USBW

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

Stainless steel auto-ground clips assure positive ground

FIELD USES/VERTICAL MARKETS

- Healthcare
- Education
- Airports
- Retail
- Hospitality/Lodging
- Office
- Institutional
- Multiple Dwelling




PASS & SEYMOUR® UL Fed Spec USB Chargers 15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Rating A	V	Color	NEMA Configuration No.
Duplex Tamper-Resistant Receptacle with USB Charger				
TR5262USB	15A	125V	Brown	5-15R
TR5262USBW	15A	125V	White	5-15R
TR5262USBLA	15A	125V	Light Almond	5-15R
TR5262USBI	15A	125V	Ivory	5-15R
TR5262USBBK	15A	125V	Black	5-15R
TR5262USBGRY	15A	125V	Gray	5-15R
TR5262USBRED	15A	125V	Red	5-15R
TR5262USBGN	15A	125V	Green	5-15R
TR5262USBNI	15A	125V	Nickel-Plated	5-15R
TR5362USB	20A	125V	Brown	5-20R
TR5362USBW	20A	125V	White	5-20R
TR5362USBLA	20A	125V	Light Almond	5-20R
TR5362USBI	20A	125V	Ivory	5-20R
TR5362USBBK	20A	125V	Black	5-20R
TR5362USBGRY	20A	125V	Gray	5-20R
TR5362USBRED	20A	125V	Red	5-20R
TR5362USBGN	20A	125V	Green	5-20R
TR5362USBNI	20A	125V	Nickel-Plated	5-20R



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

PASS & SEYMOUR®

UL Fed Spec USB Chargers

15 & 20A, 125V



TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, UL Fed Spec Listed
Complies with test requirements UL 498, UL 1310, Fed Spec WC596, CSA C22.2 No. 42, CSA C22.2 No. 223

Performance

Electrical

Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)

Mechanical

Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.
Product Identification	Ratings are permanent part of the device

Environmental

Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



Materials

Face	Polycarbonate
Body	Nylon
Contacts	CDA 260 Brass
Mounting Strap	.046" Zinc-Plated Steel
Terminal Screws	Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate For Color Identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel
Auto-Ground Clip	Stainless Steel


Warranty

1 Year

For more information on these and other P&S products refer to our Catalog or visit our web site.

SF20136 — August 2013 — For latest specs visit www.legrand.us/passandseymour

COMPLEMENTARY DEVICES & ACCESSORIES



TURNLOK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Heavy-Duty Flanged Inlets & Outlets




GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip® M3



SPD & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok® Isolated Ground
- Heavy-Duty Isolated Ground SPD
- Heavy-Duty SPD
- Construction Grade SPD



IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

ALSO AVAILABLE...

- | | | | |
|--------------------------------------|-------------------------------------|-------------------------------|----------------------------|
| ■ Hospital Grade Devices | ■ Straight Blade Plugs & Connectors | ■ Weatherproof Boxes & Covers | ■ Flexcor® Wire Mesh Grips |
| ■ SPD & Isolated Ground Devices | ■ Turnlok® Locking Devices | ■ IEC 309 Industrial Products | ■ Bulk Solutions |
| ■ Ground Continuity Monitoring (GCM) | | | |



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195
www.legrand.ca

