



Actual

Catalog Number: 2CCU
Product ID: 7TAA002750R0000
UPC Number: 04226900431
Status: Active

Two Gang Universal Flip-Lid Weatherproof Receptacle Cover, Silver, Die Cast Zinc

- Keyhole openings on back enable easy installation on an existing outlet.
- Durable, die-cast zinc-alloy construction.
- Lockable for security when not in use.
- Preconfigured for GFCI, the industry's most common outdoor application.
- Capable of mounting either vertically or horizontally.
- Easy access to outlet with 130 degree opening

North American Specifications (UNSPSC)

UNSPSC	39121304 Electrical box covers
IGCC	4425 Electrical box covers
Brand Name	Red Dot
Type	Universal Flip-Lid Weatherproof Covers
Special Features	Included adapter plates offer 12 installation options with 1-gang cover and 25 installation options with 2-gang cover.
Application	Suitable for use in wet locations with cover closed
Standard	UL E28688
Material	Zinc Die Cast
Color	Silver
Knockouts	No

European Specifications (ETIM)

ETIM	EC002656 Cover for box/housing for built-in mounting in the wall/ceiling
Length	115.887mm
Width	117.475mm
Shape	Rectangular
Type of fastening	Screw cover
Model	Mounting cover
Material	Other
Colour	Other
With screws	N

Packaging

Outer Quantity	10
Outer Dimensions (inches)	12.6x5.4x7.8
Weight Uom	80.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Marketing Brochure US 1	Available on Website
Catalog US 1	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com